
SR328B Nylon Sliding Cable Chain with un-screwable aluminium rods

Inner height (D) 48 mm Strong double share Sideband & Frame construction with large anti-friction triple-pin. The chain incorporates large sliding-skid surfaces to offer durability, even with high speed/loads. The Alu-rod frames are un-screwable from inner and outer radius. As standard the chain comes with frames every second link, on request with frames every link. Separator systems are available.



Separator	
- Unassembled	Part.no S3000F
- Assembled	Part.no S3000FMC
Pin	
	Part.no PG328TP


Technical characteristics

Speed	3,5 m/s
Acceleration	8 m/s ²

For higher requirements please consult our technical dept.

Α	В	С	D	R	Weight/m	Chain
mm	mm	mm	mm	mm	kg	Part Number
162	79	100	48	150-180-200-230-280-400	2,50	SR328B100□□□*
212	79	150	48	150-180-200-230-280-400	2,60	SR328B150□□□*
262	79	200	48	150-180-200-230-280-400	2,75	SR328B200 □ □ □ *
312	79	250	48	150-180-200-230-280-400	2,90	SR328B250□□□*
362	79	300	48	150-180-200-230-280-400	3,00	SR328B300 □ □ □*
C+62	79		48	150-180-200-230-280-400	SR3	328B □□□□□□**

*Complete the code by inserting the value of the radius (R): Ex. SR328B100 🗓 🗓 🔯 **Complete the code by inserting the value of the quote C and the radius (R): Ex. SR328B123150 Chain equipped with aluminium rods every pitch: complete the code by inserting the letter D. Ex. SR328B100150 D



Н	N	M
mm	mm	mm
375	425	955
435	530	1220
475	600	1395
535	700	1655
635	875	2095
875	1285	3145
	mm 375 435 475 535 635	mm mm 375 425 435 530 475 600 535 700 635 875

Length of chain (L) Half travel distance $(\frac{LS}{2})$ plus length of curve (M)

$$L = \frac{LS}{2} + M$$



End Brackets

The end brackets set allows the two ends of the chain to be attached to the equipment. One set comprises two movable end brackets to install at the moving point and two standard steel end brackets to install at the fixed point.

Bright Zinc Plated Steel
Movable Type*
(moving point)
Bright Zinc Plated Steel
Type*
(fixed point)






Fig. A Chain fixed outside the radius. (Fig A)





Chain	F		
Туре	mm		
SR328B100	87		
SR328B150	137		
SR328B200	187		
SR328B250	237		
SR328B300	287		
Special dimension F=A-75			

Bright Zinc Plated Steel Type Part Numbers

Complete Set Assembled
Chain End Brackets
Type Set
SR328B... A328KM

Complete Set Unassembled
Chain End Brackets
Type Set
SR328B... A328K

*Available on request in stainless steel


Serie Slidling

SR328B Nylon Sliding Cable Chain with un-screwable aluminium rods





Supplementary movable separators.



Steel laminar cover.

Special tool to remove the connecting pivots: Part Number PZ038.



For further information please consult Brevetti Stendalto's Technical Office